

BEAKERS



Graduated Beakers

"No-Drip" Spout for Easy Pouring

Griffin low form polypropylene beakers are translucent, chemical resistant and will stack without sticking together. Raised numeric graduations show approximate volume ($\pm 5\%$). All sizes are steam autoclavable at 121°C (250°F) and microwavable.

Per pack.



CATALOG NO.	CAPACITY	PACKS/CASE	QNTY/PACK
F26210-0000	50ml	4	12
F26211-0000	100ml	4	12
F26212-0000	150ml	4	12
F26213-0000	250ml	6	6
F26214-0000	400ml	6	6
F26215-0000	600ml	6	4
F26216-0000	1000ml	4	3
F26217-0000	2000ml	6	1
F26219-0000	4000ml	6	1

Beaker Specifications

CATALOG NO.	GRADUATION	HEIGHT	TOP O.D.	BOTTOM O.D.
F26210-0000	Every 10ml	48.3mm (1.9")	50.8mm (2")	40.6mm (1.6")
F26211-0000	25ml	66.0mm (2.6")	64.3mm (2.53")	50.8mm (2")
F26212-0000	25ml	76.2mm (3")	73.2mm (2.88")	58.4mm (2.3")
F26213-0000	50ml	88.9mm (3.5")	83.3mm (3.28")	66.8mm (2.63")
F26214-0000	100ml	111.1mm (4.37")	96.5mm (3.8")	74.7mm (2.94")
F26215-0000	100ml	127.0mm (5")	111.0mm (4.37")	83.8mm (3.3")
F26216-0000	200ml	152.0mm (6")	130.2mm (5.13")	101.6mm (4")
F26217-0000	500ml	184.2mm (7.25")	165.1mm (6.5")	133.4mm (5.25")
F26219-0000	1000ml	235.0mm (9.25")	212.6mm (8.37")	171.5mm (6.75")

Weighted Beaker/Flask Holders

Eliminate Drifting and Tipping in Water Baths

Weighted holder grips beakers or flasks firmly in four flared stainless steel prongs. The Vikem® vinyl-coated lead ring secured beneath the holder keeps container immersed in water, provides a low center of gravity and allows water to circulate underneath the beaker. Can be used in boiling liquid up to 135°C (275°F) for 1 hour.



CATALOG NO.	FITS BEAKER	WEIGHT	DIAMETER
F18309-0100	100ml	165gm (0.36lb)	60mm (2.4")
F18309-0250	250ml	237gm (0.5lb)	80mm (3.3")